



HDA098Z

### Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 100A 18kA CTC

#### Technical Features

##### Electric current

|                                                                                           |          |
|-------------------------------------------------------------------------------------------|----------|
| Rated current                                                                             | 100 A    |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2 | 18 kA    |
| Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2   | 18 kA    |
| Rated current 10°C according to IEC 60947                                                 | 122.20 A |
| Rated current 15°C according to IEC 60947                                                 | 119.70 A |
| Rated current 20°C according to IEC 60947                                                 | 117 A    |
| Rated current 25°C according to IEC 60947                                                 | 114.40 A |
| Rated current 30°C according to IEC 60947                                                 | 111.60 A |
| Rated current at 35°C according to IEC 60947                                              | 108.80 A |
| Rated current at 40°C according to IEC 60947                                              | 106 A    |
| Rated current 45°C according to IEC 60947                                                 | 103 A    |
| Rated current 50°C according to IEC 60947                                                 | 100 A    |
| Rated current 55°C according to IEC 60947                                                 | 96.80 A  |
| Rated current at 60°C according to IEC 60947                                              | 93.60 A  |
| Rated current 65°C according to IEC 60947                                                 | 90.20 A  |
| Rated current 70°C according to IEC 60947                                                 | 86.70 A  |

##### Architecture

|                           |                 |
|---------------------------|-----------------|
| Number of poles           | 1               |
| Control/operation element | Toggle          |
| Device construction type  | Fixed built-in  |
| Neutral position          | Without neutral |

##### Tripping

|                            |       |
|----------------------------|-------|
| Response time when opening | 10 ms |
|----------------------------|-------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Voltage

|                                                  |        |
|--------------------------------------------------|--------|
| Rated impulse withstand voltage U <sub>imp</sub> | 8000 V |
| Rated insulation voltage U <sub>i</sub>          | 690 V  |

##### Functions

|           |        |
|-----------|--------|
| Trip unit | TM F/F |
|-----------|--------|

##### Power

|                                       |        |
|---------------------------------------|--------|
| Total power loss under I <sub>N</sub> | 8.40 W |
|---------------------------------------|--------|

##### Endurance

|                                        |       |
|----------------------------------------|-------|
| Electric endurance in number of cycles | 10000 |
| Number of mechanical operations        | 20000 |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

##### Connection

|                                  |                        |
|----------------------------------|------------------------|
| Cross-section flexible conductor | 4 - 70 mm <sup>2</sup> |
| Cross-section rigid conductor    | 4 - 95 mm <sup>2</sup> |

##### Installation, mounting

|                               |       |
|-------------------------------|-------|
| Mounting-/Connection Position | Front |
|-------------------------------|-------|

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

##### Settings

|                                                 |   |
|-------------------------------------------------|---|
| Thermal protection knob setting xI <sub>N</sub> | 1 |
|                                                 | 1 |

Product Datasheet

HDA098Z

---

|                               |  |          |
|-------------------------------|--|----------|
| Dimensions                    |  |          |
| Height                        |  | 130 mm   |
| Width                         |  | 25 mm    |
| Depth                         |  | 68 mm    |
| Compatibility                 |  |          |
| Suitable for DIN Rail         |  | Yes      |
| Main electrical attributes    |  |          |
| Magnetic protection trip time |  | 0 - 0 ms |
| Sustainability                |  |          |
| REACH-SVHC free               |  | Yes      |
| RoHS conform                  |  | Yes      |