



HHA101U

### Moulded Case Circuit Breaker h3 x160 TM ADJ 4P4D N0-100% 100A 25kA CTC

#### Technical Features

##### Electric current

|                                                                               |       |
|-------------------------------------------------------------------------------|-------|
| Rated current                                                                 | 100 A |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2 | 25 kA |
| Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2 | 35 kA |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2   | 25 kA |

##### Architecture

|                 |   |
|-----------------|---|
| Number of poles | 4 |
|-----------------|---|

##### Electric current

|                                                                             |       |
|-----------------------------------------------------------------------------|-------|
| Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2 | 20 kA |
|-----------------------------------------------------------------------------|-------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Voltage

|                                      |             |
|--------------------------------------|-------------|
| Rated impulse withstand voltage Uimp | 8000 V      |
| Rated insulation voltage Ui          | 690 V       |
| Rated operational voltage Ue         | 220 - 415 V |

##### Functions

|           |        |
|-----------|--------|
| Trip unit | TM A/F |
|-----------|--------|

##### Power

|                           |         |
|---------------------------|---------|
| Total power loss under IN | 35,70 W |
|---------------------------|---------|

##### Endurance

|                                        |       |
|----------------------------------------|-------|
| Electric endurance in number of cycles | 10000 |
| Number of mechanical operations        | 20000 |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

##### Connection

|                                  |                        |
|----------------------------------|------------------------|
| Cross-section flexible conductor | 4 - 70 mm <sup>2</sup> |
| Cross-section rigid conductor    | 4 - 95 mm <sup>2</sup> |

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

##### Settings

|                                     |                  |
|-------------------------------------|------------------|
| Thermal protection knob setting xIN | 0,63<br>0,8<br>1 |
|-------------------------------------|------------------|

##### Dimensions

|        |        |
|--------|--------|
| Height | 130 mm |
| Width  | 100 mm |
| Depth  | 68 mm  |

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |