



BD464

Earth leakage add-on block 4P 63A 30mA AC Class

Technical Features

Architecture

| | |
|------------------|------|
| Neutral position | Left |
| Number of poles | 4 |

Capacity

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Voltage

| | |
|---|-------------|
| Rated operational voltage U_e | 230 - 400 V |
| Rated insulation voltage U_i | 500 V |
| Rated impulse withstand voltage U_{imp} | 4000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Electric current

| | |
|---|-------|
| Rated residual operating current I_{dn} | 30 mA |
| Rated current | 63 A |

Connectivity

| | |
|---|------------------|
| Down connection alignment for modular devices | Aligned terminal |
|---|------------------|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.90 - 2.90 Nm |

Dimensions

| | |
|--------|-------|
| Height | 70 mm |
| Width | 35 mm |
| Depth | 92 mm |