



HEW250JR

**Moulded Case Circuit Breaker h3+ P630 LSI 3P3D 250A 70kA FTC**

**Technical Features**

**Electric current**

Rated current	250 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 230 V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 415 V AC IEC 60947-2	70 kA
Breaking capacity on 1-pole for AC 230 V IEC 60947-2	10 kA
Breaking capacity on 1-pole for AC 400 V IEC 60947-2	10 kA

**Architecture**

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Electric current**

Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 690 V AC IEC 60947-2	12 kA
Rated service breaking capacity I <sub>cs</sub> under 220 V AC according to IEC 60947-2	100 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	100 kA
Rated service breaking capacity I <sub>cs</sub> under 240 V AC according to IEC 60947-2	100 kA
Rated service breaking capacity I <sub>cs</sub> under 380 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I <sub>cs</sub> under 415 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I <sub>cs</sub> under 690 V AC according to IEC 60947-2	12 kA
Rated current 10°C according to IEC 60947	250 A
Rated current 15°C according to IEC 60947	250 A
Rated current 20°C according to IEC 60947	250 A
Rated current 25°C according to IEC 60947	250 A
Rated current 30°C according to IEC 60947	250 A
Rated current at 35°C according to IEC 60947	250 A
Rated current at 40°C according to IEC 60947	250 A
Rated current 45°C according to IEC 60947	250 A
Rated current 50°C according to IEC 60947	250 A
Rated current 55°C according to IEC 60947	250 A
Rated current at 60°C according to IEC 60947	250 A
Rated current 70°C according to IEC 60947	250 A
Rated current 65°C according to IEC 60947	250 A

**Settings**

I <sub>r1</sub> current dial setting	90 A
	100 A
	110 A
	125 A
	140 A
	160 A
	180 A
	200 A
	225 A
	250 A
Adjustment range short-term delayed short-circuit release	122.85 - 2500.0 A

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	18 - 18 Nm
Mounting-/Connection Position	Front

**Voltage**

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 690 V

**Functions**

Trip unit	LSI
-----------	-----

**Power**

Total power loss under IN	36.8 W
Power loss per pole at In	12.3 W

**Equipment**

Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Connection**

Connector/plug type	Terminal
---------------------	----------

**Cable**

Cable material	Copper
----------------	--------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

**Dimensions**

Height	260 mm
Width	140 mm
Depth	150 mm

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Compatibility**

Suitable for DIN Rail	No
Compatible with RDC AOB	Yes
Suitable for distribution board	Yes

**Power supply**

Position power supply	Bidirectional
-----------------------	---------------

**Electrical protection**

Long-time overload protection (ltd): delay (tr)	0.5 s
	1.5 s
	2.5 s
	5 s
	7.5 s
	9 s
	10 s
	12 s
	14 s
	16 s
	Short-time protection (std): current (Isd)
2	
3	
4	
5	
6	
7	
8	
8	
10	

---

**Electrical protection**

Short-time protection (std): delay (tsd)	50 ms 100 ms 200 ms 300 ms 400 ms
--	---

---

Instantaneous protection (li): dial setting coefficient	3 4 5 6 7 8 10 11 12
---	--

---

**Sustainability**

RoHS conform	Yes
--------------	-----

---