



VML1010

**Dual Row 4+6 Way 100A Switch 2\*100A 30mA RCCB**

**Technical Features**

**Installation, mounting**

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

**Architecture**

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

**Functions**

|                            |     |
|----------------------------|-----|
| Has protection main switch | Yes |
|----------------------------|-----|

**Capacity**

|                   |    |
|-------------------|----|
| Number of modules | 10 |
|-------------------|----|

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

**Dimensions**

|        |        |
|--------|--------|
| Depth  | 100 mm |
| Height | 485 mm |
| Width  | 225 mm |

**Cover, door**

|                           |    |
|---------------------------|----|
| Interlockable             | No |
| Door/cover is transparent | No |

**Materials**

|          |            |
|----------|------------|
| RAL code | 9010       |
| Colour   | Pure white |
| Material | Steel      |

**Connection**

|                             |   |
|-----------------------------|---|
| Number of accessible phases | 2 |
|-----------------------------|---|

**Scope of delivery**

|  |   |
|--|---|
| Number of earth leakage circuit breaker type A | 2 |
| Number of RCCB in enclosure                    | 2 |

**Equipment**

|                    |    |
|--------------------|----|
| Number of rows     | 2  |
| Number of rails    | 2  |
| With socket outlet | No |

**Safety**

|                               |       |
|-------------------------------|-------|
| Ingress Protection (IP) class | IP2XC |
|-------------------------------|-------|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|