



WGMS115S

15A SINGLE SWITCHED SOCKET

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Output current	0 mA
Rated current	15 A

Voltage

Output voltage	0-0 V
----------------	-------

Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Output power	0 W
Power consumption standby	0 W

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

Dimensions

Height	34 mm
Width	86 mm
Depth	22 mm

Cable

Cable length	0 m
--------------	-----

Dimensions

Built-in depth flush-mounted boxes	35 mm
Built-in depth	22 mm

Connection

Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0.08 - 4 mm ²
Number of conduit inlets	0

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Back

Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	British Standard

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Equipment

With lock	No
-----------	----

Accessories

Has labelling field	No
---------------------	----

Pre-equipped with	None
-------------------	------

Capacity

Number of modules	0
-------------------	---

Safety

With enhanced contact protection	No
----------------------------------	----

Impact resistance IK	IK02
----------------------	------

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

Identification

With imprint	No
--------------	----

Suitable for

shark	
-------	--

Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----
