



EZN005



Symmetrical Flasher

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Power consumption during operation	15 VA
Power loss at full load	2 W
230 V incandescent and halogen lamp	450 W

Use conditions

Operating temperature	-20 - 50 °C
Storage/transport temperature	-40 - 70 °C

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²
Number of contacts	1
Type of contacts	1x changeover

Capacity

Number of modules	1
-------------------	---

Texts

Switch mode	Change-over contact, usable as NC or NO
Function	Functions: On delay, off delay, single shot leading edge/single shot trailing edge, pulse shaping, flashing symmetrically, contact open/closed
Type of connection	With screw terminals
Installation mode	For mounting on DIN rail

Dimensions

Height	85 mm
Width	17.50 mm
Depth	58 mm

Electric current

Acceptable current rating AC1	8 A
-------------------------------	-----

Equipment

Number of NC contacts	0
Number of NO contacts	0
Switch off delay	Yes
Switch on delay	Yes

Settings

Time delay	0.1 S - 10 h
------------	--------------

Voltage

Type voltage supply	AC/DC
---------------------	-------

Illustrations | Drawings

