

Product Datasheet

SPA080



SPA080

Cartridge L-N Uc 264V Iimp 25kA Imax 50kA Up 1.5kV for SPA180

Technical Features

Electric current

Max. discharge (Imax) L-N(PEN)/ N-PE	50 kA
--------------------------------------	-------

Network configuration

Network type	TN
--------------	----

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Electric current

Lightning impulse current Iimp (10/350 µs) IEC 61643 L-N(PEN)/ N-PE	25 kA
---	-------

Equipment

With remote signalling contact	Yes
--------------------------------	-----

Capacity

Number of modules	2
-------------------	---

Voltage

Voltage protection level Up according to IEC 61643-1	1.50 kV
Continuous operating voltage Uc according to IEC 61643-1	264 V
Rated operational voltage Ue	240 - 240 V
Voltage level Up L-N/PEN IEC 61643-11	1.5 kV

Architecture

Number of poles	1
-----------------	---

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Dimensions

Height	113.4 mm
Width	35.50 mm
Depth	64.2 mm

Controls and indicators

With indicator lamp	Yes
---------------------	-----

Standards

Requirement class IEC 61643	T1
	T2

Frequency

Frequency	50 - 60 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Sustainability

RoHS conform	Yes
--------------	-----