



dr80f4

Din rail board, 5 row 80M, non-transparent door, flush

Technical Features

Voltage

Nominal voltage	415 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Flush mounting
-------------	----------------

Power

Maximum power loss per cabinet at $\Delta T=20K$	35.39 W
--	---------

Equipment

Number of rails	5
-----------------	---

Number of rows	5
----------------	---

With lock	No
-----------	----

Has neutral terminal block	Yes
----------------------------	-----

Capacity

Number of modules	80
-------------------	----

Number of half modules terminals per rail	32
---	----

Functions

Has protection main switch	No
----------------------------	----

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	949 mm
--------	--------

Width	430 mm
-------	--------

Depth	5 mm
-------	------

Built-in height	920 mm
-----------------	--------

Built-in width	400 mm
----------------	--------

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	110 mm
----------------	--------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	16
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	17
--------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
----------	-------

RAL code	9010
----------	------

Colour	Grey white
--------	------------

Equipment

Has earthing terminal block	No
-----------------------------	----

Has mounting plate	No
--------------------	----

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP40
Locking type	Without lock
Glow wire test	960 °C

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes