



WBP115S

Technical Features

Electric current

Rated current

15 A

Frequency

Frequency

50 - 50 Hz

Materials

Colour

White

Dimensions

Height

77 mm

Width

117 mm

Installation, mounting

Mounting on

Flush mounting

Connectivity

Type of connection

Screw terminal

Mounting type

Screw mounting

Equipment

Connector/plug type socket outlet

Australian standard AS/NZS 3112

Rotated central insert

No

With hinged lid

No

Accessories

Has labelling field

No

Capacity

Number of modules

1

Safety

Ingress Protection (IP) class

IP20

Functions

With orientation lighting

No

With function lighting

No

Texts

Imprint

Without imprint

Cover

Full cover plate

Type of connection

With screw terminals

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes