

Product Datasheet

WGCXEDR500KB



WGCXEDR500KB

40-500W single dimmer;kb

Technical Features

Voltage

| | |
|------------------------------|---------|
| Operating voltage | 0-230 V |
| Rated operational voltage Ue | 0-230 V |

Connectivity

| | |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

Frequency

| | |
|-----------|----------|
| Frequency | 50-60 Hz |
|-----------|----------|

Electric current

| | |
|-----------------|-------------|
| Control current | 170-2170 mA |
|-----------------|-------------|

Materials

| | |
|----------|--------------------|
| Colour | Knight black |
| Material | Polycarbonate (PC) |

Dimensions

| | |
|----------------|-------|
| Built-in depth | 34 mm |
| Height | 41 mm |
| Width | 86 mm |
| Depth | 41 mm |

Architecture

| | |
|---------------------------|--------|
| Control/operation element | Dimmer |
|---------------------------|--------|

Power

| | |
|-------------------------------------|----------|
| 230 V incandescent and halogen lamp | 500 W |
| Power incandescent lamp | 40-500 W |

Lighting

| | |
|-------------------------|----------|
| Dimmable 230 V LED lamp | 40-250 W |
| LED lamp power | 40 W |

Use conditions

| | |
|-----------------------|----------|
| Operating temperature | -5-45 °C |
|-----------------------|----------|

Connection

| | |
|----------------------------------|---------------------------|
| Cross-section rigid conductor | 1.5 - 2.5 mm ² |
| Cross-section flexible conductor | 1.5 - 2.5 mm ² |

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|