



WFDP50VNBSW

### 50A Double Pole Switch 2 Gang with LED Indicator Brushed Steel White Insert

#### Technical Features

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Materials

Colour	Stainless steel
Surface finish	Matt
Material	Stainless steel
Treatment	Brushed

##### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Dimensions	86 x 86 mm
Built-in depth	29.10 mm

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Electric current

Rated current	50 A
---------------	------

##### Texts

Lighting	With control LED for ON
Switch mode	2-pole

##### Sustainability

RoHS conform	Yes
--------------	-----