



NRN300

MCB 3P 25kA C-0.5A 3M

Technical Features

Electric current

Rated current	0.50 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	7.50 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	25 kA
Rated current -25°C	0.69 A
Rated current -10°C	0.64 A
Rated current at -20°C	0.67 A
Rated current -15°C	0.66 A
Rated current -5°C	0.63 A
Rated current at 0°C	0.61 A
Rated current 5°C	0.59 A
Rated current 10°C	0.58 A
Rated current 15°C	0.56 A
Rated current at 20°C	0.54 A
Rated current 25°C	0.52 A
Rated current 30°C	0.50 A
Rated current 35°C	0.48 A
Rated current at 40°C	0.45 A
Rated current at 45°C	0.43 A
Rated current at 50°C	0.40 A
Rated current 55°C	0.37 A
Rated current 60°C	0.34 A
Rated current 65°C	0.31 A
Rated current 70°C	0.27 A

Architecture

Type of pole	3P
Curve	C

Capacity

Number of modules	3
-------------------	---

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
---	-------

Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

Voltage

Rated operational voltage Ue	415 - 415 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for massive conductors	1 - 35 mm ²

Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Class of energy limitation I ² t	3
---	---

Air humidity protection	For all climates
-------------------------	------------------

Operating temperature	-25 - 70 °C
-----------------------	-------------

Power

Total power loss under IN	4.35 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	4000
--	------

Number of mechanical operations	20000
---------------------------------	-------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Top connection alignment for modular devices	Aligned terminal
--	------------------

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	83 mm
--------	-------

Width	52.50 mm
-------	----------

Depth	70 mm
-------	-------
