



NT132C

MCB 1P 10kA C-32A 1M

Technical Features

Electric current

| | |
|---|---------|
| Rated current | 32 A |
| Rated short-circuit breaking capacity I _{cn} under 230 V AC according to IEC 60898-1 | 10 kA |
| Rated current -15°C | 37.50 A |
| Rated current -10°C | 37 A |
| Rated current -5°C | 36.40 A |
| Rated current at 0°C | 35.80 A |
| Rated current 5°C | 35.20 A |
| Rated current 10°C | 34.60 A |
| Rated current 15°C | 33.90 A |
| Rated current at 20°C | 33.30 A |
| Rated current 25°C | 32.70 A |
| Rated current 30°C | 32 A |
| Rated current 35°C | 31.30 A |
| Rated current at 40°C | 30.60 A |
| Rated current at 45°C | 29.90 A |
| Rated current at 50°C | 29.20 A |
| Rated current 55°C | 28.50 A |
| Rated current 60°C | 27.70 A |
| Rated current 65°C | 27 A |
| Rated current 70°C | 26.30 A |

Architecture

| | |
|--------------|----|
| Type of pole | 1P |
| Curve | C |

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical attributes

| | |
|---|-------|
| Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1 | 10 kA |
|---|-------|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque top terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

Voltage

| | |
|--|-------------|
| Rated operational voltage U _e | 240 - 415 V |
| Type voltage supply | AC |
| Rated insulation voltage U _i | 500 V |
| Rated impulse withstand voltage U _{imp} | 4000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Connection

| | |
|--|------------------------|
| Cross-section of input and output with screws, for massive conductors | 1 - 35 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for massive conductors | 1 - 35 mm ² |

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect |
| Type of top connection for modular devices | Screw terminal |
| 360° mounting position possible | Yes |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Safety

| | |
|---------------|-------|
| Grid distance | 35 mm |
|---------------|-------|

Use conditions

| | |
|--|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
|--|---|

| | |
|---|---|
| Class of energy limitation I ² t | 3 |
|---|---|

| | |
|-------------------------|------------------|
| Air humidity protection | For all climates |
|-------------------------|------------------|

| | |
|-----------------------|-------------|
| Operating temperature | -25 - 70 °C |
|-----------------------|-------------|

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 4.40 W |
|---------------------------|--------|

Connectivity

| | |
|--|------------------|
| Top connection alignment for modular devices | Aligned terminal |
|--|------------------|

| | |
|---|------------------|
| Down connection alignment for modular devices | Aligned terminal |
|---|------------------|

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Dimensions

| | |
|--------|-------|
| Height | 83 mm |
|--------|-------|

| | |
|-------|----------|
| Width | 17.50 mm |
|-------|----------|

| | |
|-------|-------|
| Depth | 70 mm |
|-------|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|
