



ERC418

**Relay 16A, 2NO+2NC, 230V~50Hz**

**Technical Features**

**Connection**

Type of contacts	2NC+2NO
------------------	---------

**Electric current**

Rated current	16 A
---------------	------

**Capacity**

Number of modules	2
-------------------	---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	4000 V
--------------------------------------	--------

Rated insulation voltage Ui	440 V
-----------------------------	-------

Rated operational voltage Ue	400 - 400 V
------------------------------	-------------

Command voltage AC	230 - 230 V
--------------------	-------------

Command voltage DC	0 - 0 V
--------------------	---------

**Use conditions**

Operating temperature	-10 - 50 °C
-----------------------	-------------

**Use**

Category of use	AC-7a/AC-7b
-----------------	-------------

**Use conditions**

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

**Endurance**

Number of mechanical operations	1000000
---------------------------------	---------

Electric endurance in number of cycles	30000
--	-------

**Power**

Total power loss under IN	3.50 W
---------------------------	--------

Inrush power absorbed	21 VA
-----------------------	-------

**Dimensions**

Height	83 mm
--------	-------

Width	35.75 mm
-------	----------

Depth	60 mm
-------	-------

**Connection**

Number of contacts	4
--------------------	---

**Equipment**

Number of NO contacts	2
-----------------------	---

Number of NC contacts	2
-----------------------	---

With switch for manual switch	Yes
-------------------------------	-----

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
----------------------------------	-----------------------

Cross-section rigid conductor	1 - 10 mm <sup>2</sup>
-------------------------------	------------------------

**Installation, mounting**

Nominal tightening torque	1.20 - 1.20 Nm
---------------------------	----------------

**Sustainability**

RoHS conform	Yes
--------------	-----