



20316086



Temp. cont.,NCcontact,Cen. plate,24V AC/DC,rocker switch,Q.1/Q.3,ant.velv.lacq.

### Technical Features

#### Architecture

Control/operation element	Rotative
---------------------------	----------

#### Electric current

Rated current	4 A
Max. switching current	10 A

#### Voltage

Nominal voltage	24 - 24 V
-----------------	-----------

#### Power supply

Supply voltage	24 V AC/DC
----------------	------------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Settings

Comfort temperature setpoint	5 - 30 °C
------------------------------	-----------

#### Materials

Colour	Anthracite
RAL code	7016
Surface finish	Velvety
Material	Metal Plastic

#### Dimensions

Height	71 mm
Width	71 mm
Depth	50.90 mm

#### Screen

With display	No
--------------	----

#### Equipment

Switching temperature difference	0.50 K
Type of thermostat	Room thermostat
Type of probe	Bimetal

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Connection

Type of contacts	1NC
------------------	-----

#### Compatibility

Type of HVAC control	Heating
----------------------	---------

#### Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

#### Texts

Installation mode	Without spreader claws
Type of connection	With plug-in terminals
Thermal re-circulation	With thermal return
Imprint	With imprint
Junction	With separate connection for night lowering

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes