



SBN240

**2-pole, 63A Modular Switch with big terminals**

**Technical Features**

**Architecture**

Number of poles	2
Neutral position	Without neutral
Type of pole	2P

**Electric current**

Rated current	63 A
Rated conditional short-circuit current I <sub>cc</sub> with gI-gG fuses	0.94 kA
Acceptable current rating AC21 category A	63 A
Acceptable current rating AC21 category B	63 A
Acceptable current rating AC22 category A	63 A
Acceptable current rating AC22 category B	63 A
Rated short-circuit making capacity I <sub>cm</sub> under 415 V AC according to IEC 60947-3	1.33 kA
Rated short-time withstand current I <sub>cw</sub> 1s IEC 60947	0.94 kA

**Installation, mounting**

Nominal tightening torque	3.60 - 3.60 Nm
---------------------------	----------------

**Voltage**

Rated operational voltage U <sub>e</sub>	400 - 400 V
Type voltage supply	AC
Rated insulation voltage U <sub>i</sub>	440 V

**Installation, mounting**

Type of bottom connection for modular devices	Screw terminal
---	----------------

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	6000 V
--	--------

**Capacity**

Number of modules	2
-------------------	---

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Dimensions**

Height	83 mm
Width	35 mm
Depth	68 mm
Dimensions	83 x 35 mm

**Equipment**

Number of NO contacts	2
Number of NC contacts	0

**Use conditions**

Operating temperature	-20 - 70 °C
Storage/transport temperature	-40 - 80 °C

**Connection**

Cross-section flexible conductor	6 - 35 mm <sup>2</sup>
Cross-section rigid conductor	6 - 50 mm <sup>2</sup>

**Endurance**

Number of mechanical operations	40000
Electrical durability at nominal load in AC21 in operating cycles	2500
Electrical durability at nominal load in AC22 in operating cycles	2500

---

**Power**

Total power loss under IN	4.40 W
Power loss per pole at In	2.20 W

**Connectivity**

Down connection alignment for modular devices	Aligned terminal
Top connection alignment for modular devices	Aligned terminal

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes