



HZI815

ATS controller for Remotely operated Transfer Switching Equipment (HIB) only

Technical Features

Voltage

Rated operational voltage U _e	240 - 415 V
--	-------------

Connection

Cross-section output with rigid conductor	1.5 - 2.5 mm ²
Cross-section output with flexible conductor	1.5 - 2.5 mm ²
Connection type bus input	Screw terminal
Connection type input	Screw terminal
Output connection type	Screw terminal

Equipment

Number of outputs	4
Number of inputs	5
Type of display	LCD

Use conditions

Operating temperature	-25 - 70 °C
Storage/transport temperature	-30 - 70 °C

Installation, mounting

Mounting on	DIN rail
-------------	----------

Power

Power absorbed	10 W
----------------	------

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Installation, mounting

Nominal tightening torque of the control and auxiliary contact circuit	0.58 - 0.58 Nm
--	----------------