

# Product Datasheet

## WMDP50VN



WMDP50VN

### 50A Double Pole Switch 2 Gang Vertical with LED Indicator

#### Technical Features

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

##### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Dimensions	86 x 86 mm
Built-in depth	22.60 mm
Built-in depth flush-mounted boxes	35 mm

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Electric current

Rated current	50 A
---------------	------

##### Texts

Lighting	With control LED for ON
Switch mode	2-pole