



HPW631NR

Moulded Case Circuit Breaker h3+ P630 Energy 4P4D N0-50-100% 630A 110kA FTC

Technical Features

Electric current

Rated current	630 A
---------------	-------

Architecture

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Left

Electric current

Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	110 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	125 kA
Rated ultimate short-circuit breaking capacity Icu under 415 V AC IEC 60947-2	110 kA
Rated ultimate short-circuit breaking capacity Icu under 690 V AC IEC 60947-2	12 kA
Rated service breaking capacity Ics under 220 V AC according to IEC 60947-2	125 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	125 kA
Rated service breaking capacity Ics under 240 V AC according to IEC 60947-2	125 kA
Rated service breaking capacity Ics under 380 V AC according to IEC 60947-2	110 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	110 kA
Rated service breaking capacity Ics under 415 V AC according to IEC 60947-2	110 kA
Rated service breaking capacity Ics under 690 V AC according to IEC 60947-2	12 kA
Rated current 10°C according to IEC 60947	630 A
Rated current 15°C according to IEC 60947	630 A
Rated current 20°C according to IEC 60947	630 A
Rated current 25°C according to IEC 60947	630 A
Rated current 30°C according to IEC 60947	630 A
Rated current at 35°C according to IEC 60947	630 A
Rated current at 40°C according to IEC 60947	630 A
Rated current 45°C according to IEC 60947	630 A
Rated current 50°C according to IEC 60947	630 A
Rated current 55°C according to IEC 60947	630 A
Rated current at 60°C according to IEC 60947	623 A
Rated current 65°C according to IEC 60947	560 A
Rated current 70°C according to IEC 60947	497 A

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 690 V

Power

Total power loss under IN	119 W
---------------------------	-------

Functions

Trip unit	ENERGY
-----------	--------

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Installation, mounting

Nominal tightening torque	18 - 18 Nm
Mounting-/Connection Position	Front

Cable

Cable material	Copper Aluminium
----------------	---------------------

Compatibility

Compatible with RDC AOB	Yes
Suitable for DIN Rail	No
Suitable for distribution board	Yes

Dimensions

Height	260 mm
Width	185 mm
Depth	150 mm

Settings

Adjustment range short-term delayed short-circuit release	341.25 - 6300.0 A
---	-------------------

Electrical protection

Long-time overload protection (ltd): delay (tr)	0.5 s	
	1.5 s	
	2.5 s	
	5 s	
	7.5 s	
	9 s	
	10 s	
	12 s	
	14 s	
	16 s	
	Short-time protection (std): current (Isd)	1.5
		2
		2.5
3		
3.5		
4		
4.5		
5		
5.5		
6		
Short-time protection (std): delay (tsd)	50 ms	
	100 ms	
	200 ms	
	300 ms	
	400 ms	
Instantaneous protection (li): dial setting coefficient	3	
	3.5	
	4	
	4.5	
	5	
	5.5	
	6	
	6.5	
	7	
	7.5	
	8	
8.5		
9		
9.5		
10		
10.5		
11		

Sustainability

RoHS conform	Yes
--------------	-----