

# Product Datasheet

## HDA038Z



HDA038Z

### Moulded Case Circuit Breaker X160 1P 18kA 40A

#### Technical Features

##### Electric current

Rated current	40 A
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	18 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	18 kA
Rated current 10°C according to IEC 60947	50.10 A
Rated current 15°C according to IEC 60947	49 A
Rated current 20°C according to IEC 60947	47.80 A
Rated current 25°C according to IEC 60947	46.60 A
Rated current 30°C according to IEC 60947	45.30 A
Rated current at 35°C according to IEC 60947	44 A
Rated current at 40°C according to IEC 60947	42.70 A
Rated current 45°C according to IEC 60947	41.40 A
Rated current 50°C according to IEC 60947	40 A
Rated current 55°C according to IEC 60947	38.50 A
Rated current at 60°C according to IEC 60947	37 A
Rated current 65°C according to IEC 60947	35.40 A
Rated current 70°C according to IEC 60947	33.70 A

##### Architecture

Number of poles	1
Control/operation element	Toggle
Device construction type	Fixed built-in

##### Tripping

Response time when opening	10 ms
----------------------------	-------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	690 V

##### Functions

Trip unit	TM F/F
-----------	--------

##### Power

Total power loss under IN	3.70 W
---------------------------	--------

##### Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

##### Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

##### Connection

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>

##### Installation, mounting

Nominal tightening torque	6 - 6 Nm
Mounting-/Connection Position	Front

##### Connectivity

Type of connection	Screw terminal
--------------------	----------------

# Product Datasheet

## HDA038Z

---

### Settings

Thermal protection knob setting xIN	1
Adjustment range short-term delayed short-circuit release	0 - 0 A

### Compatibility

Suitable for DIN Rail	No
-----------------------	----

### Main electrical attributes

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------