

Product Datasheet

ESD463S



ESD463S

Humfree Contactor 63A, 4NO, 24V~ 50Hz & 24V DC

Technical Features

Connection

| | |
|------------------|-----|
| Type of contacts | 4NO |
|------------------|-----|

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Capacity

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Voltage

| | |
|--------------------------------------|-------------|
| Rated impulse withstand voltage Uimp | 4000 V |
| Rated insulation voltage Ui | 440 V |
| Rated operational voltage Ue | 400 - 400 V |
| Command voltage AC | 24 - 24 V |
| Command voltage DC | 24 - 24 V |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10 - 50 °C |
|-----------------------|-------------|

Use

| | |
|-----------------|-------------|
| Category of use | AC-7a/AC-7b |
|-----------------|-------------|

Use conditions

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -40 - 80 °C |
|-------------------------------|-------------|

Endurance

| | |
|---------------------------------|--------|
| Number of mechanical operations | 100000 |
|---------------------------------|--------|

Texts

| | |
|-------------|---|
| Safety hint | Humfree contactors are not suitable for intensive use cases (powered 24/7) and in these cases industrial contactors must be used. |
|-------------|---|

Endurance

| | |
|--|-------|
| Electric endurance in number of cycles | 30000 |
|--|-------|

Power

| | |
|---------------------------|---------|
| Total power loss under IN | 24.50 W |
| Inrush power absorbed | 5.20 VA |

Dimensions

| | |
|--------|-------|
| Height | 85 mm |
| Width | 54 mm |
| Depth | 60 mm |

Connection

| | |
|--------------------|---|
| Number of contacts | 4 |
|--------------------|---|

Equipment

| | |
|-------------------------------|----|
| Number of NO contacts | 4 |
| Number of NC contacts | 0 |
| With switch for manual switch | No |

Connection

| | |
|----------------------------------|--------------------------|
| Cross-section flexible conductor | 1.5 - 16 mm ² |
| Cross-section rigid conductor | 1.5 - 25 mm ² |

Product Datasheet
ESD463S

| Sustainability | |
|----------------|-----|
| RoHS conform | Yes |