



AE956B

**RCBO 1P+N 6kA C-6A 100mA AC Class**

**Technical Features**

**Architecture**

Type of pole	1P+N
Curve	C

**Electric current**

Rated current	6 A
Rated residual operating current I <sub>dn</sub>	100 mA
Rated current -25°C	7.20 A
Rated current at -20°C	7.10 A
Rated current -15°C	7 A
Rated current -10°C	6.90 A
Rated current -5°C	6.80 A
Rated current at 0°C	6.70 A
Rated current 5°C	6.60 A
Rated current 10°C	6.50 A
Rated current 15°C	6.40 A
Rated current at 20°C	6.20 A
Rated current 25°C	6.10 A
Rated current 30°C	6 A
Rated current 35°C	5.90 A
Rated current at 40°C	5.80 A
Rated current at 45°C	5.70 A
Rated current at 50°C	5.60 A
Rated current 55°C	5.50 A
Rated current 60°C	5.40 A
Correction factor of rating current for 2 devices placed side by side	1
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85

**Safety**

Residual current type	AC
Ingress Protection (IP) class	IP20

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Voltage**

Rated insulation voltage U <sub>i</sub>	500 V
---	-------

**Electric current**

Rated service breaking capacity I <sub>cs</sub> AC according to IEC 60898-1	6 kA
---	------

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Max. operating voltage	240 V
Rated operational voltage U <sub>e</sub>	240 - 240 V
Overvoltage category according to IEC 60947-1	3

**Power**

Total power loss under I <sub>N</sub>	1.90 W
---------------------------------------	--------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Use conditions**

Max. Altitude	2000 m
---------------	--------

**Installation, mounting**

Nominal tightening torque down terminal	2.10 - 2.10 Nm
Nominal tightening torque top terminal	2.10 - 2.10 Nm

**Use conditions**

Class of energy limitation I <sup>2</sup> t	3
---	---

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

**Connection**

Cross-section rigid conductor	1 - 25 mm <sup>2</sup>
-------------------------------	------------------------

**Installation, mounting**

Nominal tightening torque	2.10 - 2.10 Nm
---------------------------	----------------

**Capacity**

Number of modules	2
-------------------	---

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

**Dimensions**

Height	83 mm
Width	35 mm
Depth	68 mm

**Use conditions**

Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Air humidity protection	For all climates

**Sustainability**

RoHS conform	Yes
--------------	-----