

# Product Datasheet

## WGCXS216EANB



WGCXS216EANB

### 16A TWIN EURO-AMERICAN SOCKET, NB

#### Technical Features

##### Electric current

|                |      |
|----------------|------|
| Rated current  | 16 A |
| Output current | 0 mA |

##### Voltage

|                 |           |
|-----------------|-----------|
| Rated voltage   | 250 V     |
| Nominal voltage | 220-250 V |
| Output voltage  | 0-0 V     |

##### Use conditions

|                       |           |
|-----------------------|-----------|
| Operating temperature | -20-45 °C |
|-----------------------|-----------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Power

|                           |     |
|---------------------------|-----|
| Output power              | 0 W |
| Power consumption standby | 0 W |

##### Materials

|                                                        |                    |
|--------------------------------------------------------|--------------------|
| Colour                                                 | Bronze             |
| Surface finish                                         | Matt               |
| Material                                               | Polycarbonate (PC) |
| Treatment                                              | Coated             |
| Contains recycled material (% of total plastic weight) | 0 %                |

##### Dimensions

|                                    |       |
|------------------------------------|-------|
| Height                             | 30 mm |
| Width                              | 86 mm |
| Depth                              | 20 mm |
| Built-in depth flush-mounted boxes | 35 mm |
| Built-in depth                     | 20 mm |

##### Connection

|                                                          |                          |
|----------------------------------------------------------|--------------------------|
| Connector/plug type                                      | NEMA                     |
| Cross-section flexible conductor without wire end sleeve | 0.08 - 4 mm <sup>2</sup> |

##### Installation, mounting

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Back           |

##### Connectivity

|                         |                |
|-------------------------|----------------|
| Type of connection      | Screw terminal |
| With claw mounting      | No             |
| Mounting type           | Screw mounting |
| Connector/plug type USB | NEMA           |

##### Equipment

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert            | No               |
| With hinged lid                   | No               |
| With round protective earth pin   | No               |
| With signal lamp                  | No               |
| With lock                         | No               |

##### Accessories

|                     |      |
|---------------------|------|
| Has labelling field | No   |
| Pre-equipped with   | None |

Product Datasheet

WGCXS216EANB

|                                  |      |
|----------------------------------|------|
| <b>Capacity</b>                  |      |
| Number of modules                | 0    |
| <b>Safety</b>                    |      |
| With enhanced contact protection | No   |
| Impact resistance IK             | IK02 |
| Ingress Protection (IP) class    | IP20 |
| <b>Functions</b>                 |      |
| With orientation lighting        | No   |
| With function lighting           | No   |
| <b>Identification</b>            |      |
| With imprint                     | No   |
| <b>Suitable for</b>              |      |
| shark                            |      |
| <b>Sustainability</b>            |      |
| Halogen free                     | Yes  |
| REACH-SVHC free                  | Yes  |
| RoHS conform                     | Yes  |