



WBQSV5

### FIN 5 Gang Switch Plate cw mechs

#### Technical Features

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Materials

Colour	White
--------	-------

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	5
-------------------	---

#### Dimensions

Dimensions	117 x 77 mm
------------	-------------

#### Safety

Ingress Protection (IP) class	IP2X
-------------------------------	------

#### Electric current

Rated current	16 A
---------------	------

#### Texts

Installation mode	For screw fastening
-------------------	---------------------

Type of connection	With screw terminals
--------------------	----------------------

Lighting	Without lighting (cannot be illuminated)
----------	------------------------------------------

Switch mode	2-way, with loop terminal
-------------	---------------------------

#### Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----