




20316089



Temp. cont., NCcontact, Cen. plate, 24V AC/DC, rocker switch,Q.1/Q.3, p.wh.velv.

Technical Features

Architecture

Control/operation element Rotative

Electric current

Rated current 4 A

Max. switching current 10 A

Voltage

Nominal voltage 24 - 24 V

Power supply

Supply voltage 24 V AC/DC

Frequency

Frequency 50 - 60 Hz

Settings

Comfort temperature setpoint 5 - 30 °C

Materials

Colour Polar white

RAL code 9010

Surface finish Velvety

Material Metal
Plastic

Dimensions

Height 71 mm

Width 71 mm

Depth 50.90 mm

Screen

With display No

Equipment

Switching temperature difference 0.50 K

Type of thermostat Room thermostat

Type of probe Bimetal

Safety

Ingress Protection (IP) class IP20

Connection

Type of contacts 1NC

Compatibility

Type of HVAC control Heating

Use conditions

Energy efficiency class I (1%)

Texts

Installation mode Without spreader claws

Type of connection With plug-in terminals

Thermal re-circulation With thermal return

Imprint With imprint

Junction With separate connection for night lowering

Sustainability

REACH-SVHC free Yes

RoHS conform Yes