



TXB302



Binary input 2 fold, flush mounted, KNX

Technical Features

Architecture

| | |
|------------|-----|
| Bus system | EIB |
|------------|-----|

Settings

| | |
|------------------------------|-------------|
| Supported configuration mode | ETS easy |
|------------------------------|-------------|

Electric current

| | |
|--------------------------|---|
| Number of entry circuits | 2 |
|--------------------------|---|

Equipment

| | |
|-----------------------------------|----|
| External signal voltage necessary | No |
|-----------------------------------|----|

Connectivity

| | |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

Equipment

| | |
|-------------------------------|----|
| Radio frequency bidirectional | No |
| With battery | No |
| With HVAC control | No |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Lighting

| | |
|-----------------|----|
| LED controlling | No |
|-----------------|----|

Materials

| | |
|----------|------------|
| Material | Plastic |
| Colour | Light grey |
| RAL code | 7035 |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP30 |
|-------------------------------|------|

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | 0 - 45 °C |
|-----------------------|-----------|

Voltage

| | |
|----------------------------|-----------------|
| Input voltage | 5 - 5 V |
| Operating voltage over bus | 21 - 32 V |
| Type voltage supply | DC |
| System supply voltage | 30 V DC Via bus |

Texts

| | |
|--------------------|--|
| Installation mode | For flush-mounted and hollow wall mounting |
| Type of connection | With pre-assembled cable |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|