



75665599



### B.IQ push-button 5gang thermostat, display, KNX - B.IQ, p. white, matt, plastic

#### Technical Features

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

##### Functions

|                                  |     |
|----------------------------------|-----|
| With room temperature controller | Yes |
|----------------------------------|-----|

##### Dimensions

|        |           |
|--------|-----------|
| Height | 178.80 mm |
| Width  | 88.50 mm  |
| Depth  | 15 mm     |

##### Equipment

|                            |    |
|----------------------------|----|
| Number of actuation points | 12 |
|----------------------------|----|

##### Controls and indicators

|                     |     |
|---------------------|-----|
| With LED indication | Yes |
|---------------------|-----|

##### Materials

|                |               |
|----------------|---------------|
| Colour         | Polar white   |
| RAL code       | 9010          |
| Material       | Thermoplastic |
| Surface finish | Matt          |

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Screen

|              |     |
|--------------|-----|
| With display | Yes |
|--------------|-----|

##### Texts

|                |  |
|----------------|--|
| Function       | For switch, push-button, dimmer, blind and thermostat functions<br>With valve protection function<br>Button help function can be activated   |
| Operating mode | Controller operating modes: comfort, standby, night and frost/heat protection mode   |
| Protection     | With dismantling protection  |
| Temperature    | Temperature measurement via internal Temperature sensor and/or external communication object (weighting ratio parameterisable)<br>Provision of the internal temperature value via communication object |

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |