

Product Datasheet

HNB202H



HNB202H

Moulded Case Circuit Breaker X250 4P 60% 40kA 200A TM

Technical Features

Electric current

Rated current	200 A
Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2	40 kA
Rated current 0°C according to IEC 60947	238.60 A
Rated current 10°C according to IEC 60947	229.80 A
Rated current 15°C according to IEC 60947	225 A
Rated current 20°C according to IEC 60947	220.20 A
Rated current 25°C according to IEC 60947	215.40 A
Rated current 30°C according to IEC 60947	210.40 A
Rated current at 35°C according to IEC 60947	205.20 A
Rated current at 40°C according to IEC 60947	200 A
Rated current 45°C according to IEC 60947	194.60 A
Rated current 50°C according to IEC 60947	189 A
Rated current 55°C according to IEC 60947	183.40 A
Rated current 5°C according to IEC 60947	234.20 A
Rated current at 60°C according to IEC 60947	177.80 A
Rated current 65°C according to IEC 60947	172 A
Rated current 70°C according to IEC 60947	166 A

Architecture

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	800 V
Rated operational voltage U _e	220 - 415 V

Functions

Trip unit	TM A/A
-----------	--------

Power

Total power loss under I _N	24.80 W
---------------------------------------	---------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	35 - 150 mm ²
Cross-section rigid conductor	35 - 185 mm ²

Settings

Thermal protection knob setting xI _N	0.63 0.8 1
Adjustment range short-term delayed short-circuit release	0 - 0 A

Compatibility

Suitable for DIN Rail	No
-----------------------	----

Product Datasheet

HNB202H

Installation, mounting	
Mounting-/Connection Position	Front
Nominal tightening torque	12 - 12 Nm
Main electrical attributes	
Magnetic protection trip time	0 - 0 ms
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes