



MCN204

### MCB 2P 6kA C-4A 2M

#### Technical Features

##### Electric current

|                                                                               |       |
|-------------------------------------------------------------------------------|-------|
| Rated current                                                                 | 4 A   |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2 | 10 kA |
| Rated current -15°C                                                           | 5 A   |
| Rated current -10°C                                                           | 4.9 A |
| Rated current -5°C                                                            | 4.8 A |
| Rated current at 0°C                                                          | 4.7 A |
| Rated current 5°C                                                             | 4.6 A |
| Rated current 10°C                                                            | 4.5 A |
| Rated current 15°C                                                            | 4.4 A |
| Rated current at 20°C                                                         | 4.2 A |
| Rated current 25°C                                                            | 4.1 A |
| Rated current 30°C                                                            | 4 A   |
| Rated current 35°C                                                            | 3.9 A |
| Rated current at 40°C                                                         | 3.8 A |
| Rated current at 45°C                                                         | 3.6 A |
| Rated current at 50°C                                                         | 3.5 A |
| Rated current 55°C                                                            | 3.3 A |
| Rated current 60°C                                                            | 3.2 A |
| Rated current 65°C                                                            | 3 A   |
| Rated current 70°C                                                            | 2.9 A |

##### Architecture

|              |    |
|--------------|----|
| Type of pole | 2P |
| Curve        | C  |

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

##### Main electrical attributes

|                                                                       |      |
|-----------------------------------------------------------------------|------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 6 kA |
|-----------------------------------------------------------------------|------|

##### Installation, mounting

|                                         |                |
|-----------------------------------------|----------------|
| Nominal tightening torque top terminal  | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

##### Voltage

|                                      |             |
|--------------------------------------|-------------|
| Rated operational voltage Ue         | 415 - 415 V |
| Type voltage supply                  | AC          |
| Rated insulation voltage Ui          | 500 V       |
| Rated impulse withstand voltage Uimp | 4000 V      |

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Connection

|                                                                        |                        |
|------------------------------------------------------------------------|------------------------|
| Cross-section of input and output with screws, for massive conductors  | 1 - 35 mm <sup>2</sup> |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for flexible conductors            | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for massive conductors             | 1 - 35 mm <sup>2</sup> |
| Cross-section flexible conductor                                       | 1 - 25 mm <sup>2</sup> |
| Cross-section rigid conductor                                          | 1 - 35 mm <sup>2</sup> |

##### Installation, mounting

|                                               |                |
|-----------------------------------------------|----------------|
| Nominal tightening torque                     | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect      |
| Type of top connection for modular devices    | Screw terminal |
| 360° mounting position possible               | Yes            |

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Use conditions

|                                                          |                  |
|----------------------------------------------------------|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2                |
| Class of energy limitation I <sup>2</sup> t              | 3                |
| Air humidity protection                                  | For all climates |
| Operating temperature                                    | -25 - 70 °C      |

Power

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 3.78 W |
|---------------------------|--------|

Connectivity

|                                               |                  |
|-----------------------------------------------|------------------|
| Type of connection                            | Screw terminal   |
| Top connection alignment for modular devices  | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

Dimensions

|        |          |
|--------|----------|
| Height | 84.60 mm |
| Width  | 35 mm    |
| Depth  | 70 mm    |

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

Illustrations | Drawings

