



20306084



therm. w. NC cont., Centre pl., rocker switch a. LED, Q.x, alu velvety, lacq.

## Technical Features

### Architecture

Control/operation element	Rotative
---------------------------	----------

### Electric current

Rated current	4 A
Switching current	10 A
Max. switching current	10 A

### Voltage

Nominal voltage	230-230 V
-----------------	-----------

### Power supply

Supply voltage	230 V AC
----------------	----------

### Frequency

Frequency	50 - 60 Hz
-----------	------------

### Settings

Comfort temperature setpoint	5 - 30 °C
------------------------------	-----------

### Materials

Colour	Aluminium
RAL code	9006
Surface finish	Velvety
Material	Metal Plastic

### Dimensions

Height	71 mm
Width	71 mm
Depth	50.90 mm

### Screen

With display	No
--------------	----

### Equipment

Switching temperature difference	0.50 K
Type of thermostat	Room thermostat
Type of probe	Bimetal
With heater	Yes

### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

### Connection

Type of contacts	1NC
------------------	-----

### Compatibility

Type of HVAC control	Heating
----------------------	---------

### Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

### Texts

Installation mode	Without spreader claws
Type of connection	With plug-in terminals
Thermal re-circulation	With thermal return
Imprint	With imprint
Junction	With separate connection for night lowering

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes