

MCB 3P 6kA B-25A 3M

**Technical Features**

**Electric current**

Rated current	25 A
Rated current -15°C	30.40 A
Rated current -10°C	29.80 A
Rated current -5°C	29.30 A
Rated current at 0°C	28.70 A
Rated current 5°C	28.10 A
Rated current 10°C	27.50 A
Rated current 15°C	26.90 A
Rated current at 20°C	26.30 A
Rated current 25°C	25.70 A
Rated current 30°C	25 A
Rated current 35°C	24.30 A
Rated current at 40°C	23.60 A
Rated current at 45°C	22.90 A
Rated current at 50°C	22.20 A
Rated current 55°C	21.40 A
Rated current 60°C	20.70 A
Rated current 65°C	20 A
Rated current 70°C	19.20 A

**Architecture**

Type of pole	3P
Curve	B

**Capacity**

Number of modules	3
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

# Product Datasheet

## MT325A

---

<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation $I^2t$	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C
<b>Power</b>	
Total power loss under IN	9.50 W
<b>Connectivity</b>	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	83 mm
Width	52.50 mm
Depth	70 mm
<b>Sustainability</b>	
RoHS conform	Yes