



SPA800

**Combined SPD T1+T2 3P Uc 350V Iimp 25kA In 25kA Up 1.5kV TCN with remote contact**

**Technical Features**

**Electric current**

Max. discharge (Imax) L-N(PEN)/ N-PE	50 kA
--------------------------------------	-------

**Network configuration**

Network type	TN-C
--------------	------

**Electric current**

Leakage-current free	Yes
Max. overcurrent protection device, parallel connection (fuse)	315 A

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Electric current**

Lightning impulse current Iimp (10/350 μs) IEC 61643 L-N(PEN)/ N-PE	25 kA
---	-------

**Equipment**

With remote signalling contact	Yes
--------------------------------	-----

**Capacity**

Number of modules	6
-------------------	---

**Voltage**

Voltage protection level Up according to IEC 61643-1	1.50 kV
Continuous operating voltage Uc according to IEC 61643-1	350 V
Rated operational voltage Ue	230 - 400 V
Voltage level Up L-N/PEN IEC 61643-11	1.5 kV

**Architecture**

Number of poles	3
-----------------	---

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Dimensions**

Height	95.20 mm
Width	106.80 mm
Depth	67 mm

**Controls and indicators**

With indicator lamp	Yes
---------------------	-----

**Standards**

Requirement class IEC 61643	T1 T2
-----------------------------	----------

**Installation, mounting**

Nominal tightening torque	4.50 - 4.50 Nm
---------------------------	----------------

**Connection**

Cross-section of input and output with screws, for flexible conductors	2.5 - 35.0 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	2.5 - 35.0 mm <sup>2</sup>
Cross-section signal contact	0.14 - 1.5 mm <sup>2</sup>

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Sustainability**

RoHS conform	Yes
--------------	-----