



HNT125DR

Moulded Case Circuit Breaker h3+ P250 TM ADJ 3P3D 125A 40kA FTC

Technical Features

Electric current

Rated current	125 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	50 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 660 V AC IEC 60947-2	6 kA
Rated ultimate short-circuit breaking capacity Icu under 690 V AC IEC 60947-2	6 kA
Rated current 10°C according to IEC 60947	151.70 A
Rated current 15°C according to IEC 60947	148.60 A
Rated current 20°C according to IEC 60947	145.50 A
Rated current 25°C according to IEC 60947	142.30 A
Rated current 30°C according to IEC 60947	139 A
Rated current at 35°C according to IEC 60947	135.60 A
Rated current at 40°C according to IEC 60947	132.20 A
Rated current 45°C according to IEC 60947	128.60 A
Rated current 50°C according to IEC 60947	125 A
Rated current 55°C according to IEC 60947	121.30 A
Rated current at 60°C according to IEC 60947	117.40 A
Rated current 65°C according to IEC 60947	113.40 A
Rated current 70°C according to IEC 60947	109.30 A

Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 690 V

Functions

Trip unit	TM A/A
-----------	--------

Power

Total power loss under IN	27.90 W
---------------------------	---------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	35 - 150 mm ²
Cross-section rigid conductor	35 - 185 mm ²

Cover, door

Interlockable	Yes
---------------	-----

Settings

Thermal protection knob setting xIN	0.63 0.8 1
-------------------------------------	------------------

Product Datasheet

HNT125DR

Cable

Cable material	Copper
	Aluminium

Compatibility

Compatible with RDC AOB	No
Suitable for DIN Rail	No
Suitable for distribution board	Yes

Dimensions

Dimensions	165 x 105 mm
Height	165 mm
Width	105 mm
Depth	97 mm

Installation, mounting

Mounting-/Connection Position	Front
Nominal tightening torque	12 - 12 Nm

Electrical protection

Instantaneous protection (li): dial setting coefficient	6
	8
	10
	13

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes