



SVN122M

**Red LED Indicator light 230VAC**

**Technical Features**

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Voltage**

|                                           |             |
|-------------------------------------------|-------------|
| Rated insulation voltage $U_i$            | 250 V       |
| Rated impulse withstand voltage $U_{imp}$ | 4000 V      |
| Rated operational voltage $U_e$           | 230 - 230 V |
| Type voltage supply                       | AC          |

**Use conditions**

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -20 - 50 °C |
| Storage/transport temperature | -40 - 80 °C |

**Connectivity**

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

**Connection**

|                                  |                           |
|----------------------------------|---------------------------|
| Cross-section flexible conductor | 0.75 - 6 mm <sup>2</sup>  |
| Cross-section rigid conductor    | 0.75 - 10 mm <sup>2</sup> |

**Power**

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 0.80 W |
|---------------------------|--------|

**Dimensions**

|        |          |
|--------|----------|
| Height | 83 mm    |
| Width  | 17.50 mm |
| Depth  | 62 mm    |

**Lighting**

|              |     |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

**Connection**

|                     |     |
|---------------------|-----|
| Type of lamp socket | Fix |
|---------------------|-----|

**Materials**

|        |     |
|--------|-----|
| Colour | Red |
|--------|-----|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Power**

|                          |      |
|--------------------------|------|
| Power per charging point | 0 kW |
|--------------------------|------|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |