



FWU72GS

FW flush encl. 168mod, with transp. door, IP30, classII, niche 1107x565x115mm

#### Technical Features

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting Hollow wall

##### Electric current

Rated current	125 A
---------------	-------

##### Equipment

Number of rails	14
Number of rows	7
Number of section in width	2
With lock	No
Has neutral terminal block	Yes

##### Capacity

Number of modules	168
-------------------	-----

##### Dimensions

Height	1153 mm
Width	603 mm
Depth	125 mm
Built-in height	1102 mm
Built-in width	603 mm

##### Cover, door

Number of cabinet doors	1
-------------------------	---

##### Dimensions

Built-in depth	112 mm
Number of width units	24

##### Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	Yes

##### Connection

Number of conduit inlets	4
--------------------------	---

##### Materials

Material	Steel
RAL code	9010
Colour	Pure white

##### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

##### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Without lock

##### Sustainability

RoHS conform	Yes
--------------	-----