



HNT250NR

Moulded Case Circuit Breaker h3+ P250 Energy 3P3D 250A 40kA FTC

Technical Features

Electric current

Rated current	250 A
---------------	-------

Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

Electric current

Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 690 V AC IEC 60947-2	6 kA
Rated service breaking capacity Ics under 220 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 240 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity Ics under 380 V AC according to IEC 60947-2	40 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	40 kA
Rated service breaking capacity Ics under 415 V AC according to IEC 60947-2	40 kA
Rated service breaking capacity Ics under 690 V AC according to IEC 60947-2	6 kA
Rated current 10°C according to IEC 60947	250 A
Rated current 15°C according to IEC 60947	250 A
Rated current 20°C according to IEC 60947	250 A
Rated current 25°C according to IEC 60947	250 A
Rated current 30°C according to IEC 60947	250 A
Rated current at 35°C according to IEC 60947	250 A
Rated current at 40°C according to IEC 60947	250 A
Rated current 45°C according to IEC 60947	250 A
Rated current 50°C according to IEC 60947	250 A
Rated current 55°C according to IEC 60947	250 A
Rated current at 60°C according to IEC 60947	250 A
Rated current 65°C according to IEC 60947	250 A
Rated current 70°C according to IEC 60947	238.30 A

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 690 V

Power

Total power loss under IN	45 W
---------------------------	------

Functions

Trip unit	ENERGY
-----------	--------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Installation, mounting

Nominal tightening torque	12 - 12 Nm
Mounting-/Connection Position	Front

Connection

Cross-section flexible conductor	35 - 150 mm ²
Cross-section rigid conductor	35 - 185 mm ²

Cover, door

Interlockable	Yes
---------------	-----

Cable

Cable material	Copper Aluminium
----------------	---------------------

Compatibility

Compatible with RDC AOB	No
Suitable for DIN Rail	No
Suitable for distribution board	Yes

Dimensions

Height	165 mm
Width	105 mm
Depth	97 mm

Settings

Adjustment range short-term delayed short-circuit release	150 - 2500 A
---	--------------

Electrical protection

Long-time overload protection (ltd): delay (tr)	0.5 s
	1.5 s
	2.5 s
	5 s
	7.5 s
	9 s
	10 s
	12 s
	14 s
	16 s
Short-time protection (std): current (lsc)	1.5
	2
	2.5
	3
	3.5
	4
	4.5
	5
	5.5
	6
	6.5
	7
	7.5
	8
	8.5
	9
	9.5
	10

Electrical protection

Short-time protection (std): delay (tsd)	50 ms
	100 ms
	200 ms
	300 ms
	400 ms
Instantaneous protection (li): dial setting coefficient	3
	3.5
	4
	4.5
	5
	5.5
	6
	6.5
	7
	7.5
	8
	8.5
	9
	9.5
	10
	10.5
	11

Sustainability

RoHS conform	Yes
--------------	-----