



HMT251NR

**Moulded Case Circuit Breaker h3+ P250 Energy 4P4D N0-50-100% 250A 50kA FTC**

**Technical Features**

**Electric current**

Rated current	250 A
---------------	-------

**Architecture**

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Left

**Electric current**

Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	65 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 415 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 690 V AC IEC 60947-2	6 kA
Rated service breaking capacity I <sub>cs</sub> under 220 V AC according to IEC 60947-2	65 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	65 kA
Rated service breaking capacity I <sub>cs</sub> under 240 V AC according to IEC 60947-2	65 kA
Rated service breaking capacity I <sub>cs</sub> under 380 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity I <sub>cs</sub> under 415 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity I <sub>cs</sub> under 690 V AC according to IEC 60947-2	6 kA
Rated current 10°C according to IEC 60947	250 A
Rated current 15°C according to IEC 60947	250 A
Rated current 20°C according to IEC 60947	250 A
Rated current 25°C according to IEC 60947	250 A
Rated current 30°C according to IEC 60947	250 A
Rated current at 35°C according to IEC 60947	250 A
Rated current at 40°C according to IEC 60947	250 A
Rated current 45°C according to IEC 60947	250 A
Rated current 50°C according to IEC 60947	250 A
Rated current 55°C according to IEC 60947	250 A
Rated current at 60°C according to IEC 60947	250 A
Rated current 65°C according to IEC 60947	250 A
Rated current 70°C according to IEC 60947	238.30 A

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	8000 V
Rated insulation voltage U <sub>i</sub>	800 V
Rated operational voltage U <sub>e</sub>	220 - 690 V

**Power**

Total power loss under I <sub>N</sub>	45 W
---------------------------------------	------

**Functions**

Trip unit	ENERGY
-----------	--------

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Installation, mounting**

Nominal tightening torque	12 - 12 Nm
Mounting-/Connection Position	Front

**Connection**

Cross-section flexible conductor	35 - 150 mm <sup>2</sup>
Cross-section rigid conductor	35 - 185 mm <sup>2</sup>

**Cover, door**

Interlockable	Yes
---------------	-----

**Cable**

Cable material	Copper Aluminium
----------------	---------------------

**Compatibility**

Compatible with RDC AOB	Yes
Suitable for DIN Rail	No
Suitable for distribution board	Yes

**Dimensions**

Height	165 mm
Width	140 mm
Depth	97 mm

**Settings**

Adjustment range short-term delayed short-circuit release	150 - 2500 A
---	--------------

**Electrical protection**

Long-time overload protection (ltd): delay (tr)	0.5 s
	1.5 s
	2.5 s
	5 s
	7.5 s
	9 s
	10 s
	12 s
	14 s
	16 s
	Short-time protection (std): current (lsc)
2	
2.5	
3	
3.5	
4	
4.5	
5	
5.5	
6	
6.5	
7	
7.5	
8	
8.5	
9	
9.5	
10	

---

**Electrical protection**

Short-time protection (std): delay (tsd)	50 ms
	100 ms
	200 ms
	300 ms
	400 ms

---

Instantaneous protection (li): dial setting coefficient	3
	3.5
	4
	4.5
	5
	5.5
	6
	6.5
	7
	7.5
	8
	8.5
	9
	9.5
	10
	10.5
	11

---

**Sustainability**

RoHS conform	Yes
--------------	-----

---