



EC350

3Ph Kwhmeter direct 63A

Technical Features

Architecture

Type of pole	3P+N
--------------	------

Electric current

Rated current	63 A
---------------	------

Capacity

Number of modules	4
-------------------	---

Connectivity

Type of connection	Direct connection
--------------------	-------------------

Dimensions

Height	90 mm
Width	72 mm

Equipment

Type of pulse generator	Electrical
-------------------------	------------

Compatibility

Suitable for	Purchase
--------------	----------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Measurement

Measuring system	Direct measurement
Type of measuring instrument	Electronic
Frequency measuring range	50 - 60 Hz

Power supply

Number of phases for power supply	4
-----------------------------------	---

Functions

Accuracy class	B
Tariff type	One-tariff

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-10 - 55 °C
Storage/transport temperature	-25 - 70 °C

Power

Power consumption VA	8.40 VA
Total power loss under IN	1.80 W

Electric current

Maximum measuring circuit current	63 A
-----------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes