



NT363C

MCB 3P 10kA C-63A 3M

Technical Features

Electric current

Rated current	63 A
---------------	------

Architecture

Type of pole	3P
--------------	----

Curve	C
-------	---

Capacity

Number of modules	3
-------------------	---

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	10 kA
-----------------------------------------------------------------------	-------

Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
----------------------------------------	----------------

Nominal tightening torque down terminal	2.80 - 2.80 Nm
-----------------------------------------	----------------

Voltage

Rated operational voltage Ue	415 - 415 V
------------------------------	-------------

Type voltage supply	AC
---------------------	----

Rated insulation voltage Ui	500 V
-----------------------------	-------

Rated impulse withstand voltage Uimp	4000 V
--------------------------------------	--------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm ²
-----------------------------------------------------------------------	------------------------

Cross-section of input and output with screws, for flexible conductors	1 - 25 mm ²
------------------------------------------------------------------------	------------------------

Cross-section of input with screws, for flexible conductors	1 - 25 mm ²
-------------------------------------------------------------	------------------------

Cross-section of input with screws, for massive conductors	1 - 35 mm ²
------------------------------------------------------------	------------------------

Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
---------------------------	----------------

Type of bottom connection for modular devices	biconnect
-----------------------------------------------	-----------

Type of top connection for modular devices	Screw terminal
--------------------------------------------	----------------

360° mounting position possible	Yes
---------------------------------	-----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
----------------------------------------------------------	---

Class of energy limitation I ² t	3
---------------------------------------------	---

Air humidity protection	For all climates
-------------------------	------------------

Operating temperature	-25 - 70 °C
-----------------------	-------------

Power

Total power loss under IN	18.10 W
---------------------------	---------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Top connection alignment for modular devices	Aligned terminal
----------------------------------------------	------------------

Down connection alignment for modular devices	Aligned terminal
-----------------------------------------------	------------------

Dimensions

Height	83 mm
--------	-------

Width	52.50 mm
-------	----------

Depth	70 mm
-------	-------

Sustainability

RoHS conform

Yes