



HDA101L

### Moulded Case Circuit Breaker h3 x160 TM FIX 4P4D 100A 18kA CTC

#### Technical Features

##### Electric current

|                                                                                           |          |
|-------------------------------------------------------------------------------------------|----------|
| Rated current                                                                             | 100 A    |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2 | 18 kA    |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2 | 25 kA    |
| Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2   | 25 kA    |
| Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2   | 18 kA    |
| Rated current 0°C according to IEC 60947                                                  | 120.50 A |
| Rated current 10°C according to IEC 60947                                                 | 120.50 A |
| Rated current 15°C according to IEC 60947                                                 | 118.10 A |
| Rated current 20°C according to IEC 60947                                                 | 115.70 A |
| Rated current 25°C according to IEC 60947                                                 | 113.20 A |
| Rated current 30°C according to IEC 60947                                                 | 110.70 A |
| Rated current at 35°C according to IEC 60947                                              | 108.10 A |
| Rated current at 40°C according to IEC 60947                                              | 105.50 A |
| Rated current 45°C according to IEC 60947                                                 | 102.70 A |
| Rated current 50°C according to IEC 60947                                                 | 100 A    |
| Rated current 55°C according to IEC 60947                                                 | 97.10 A  |
| Rated current 5°C according to IEC 60947                                                  | 118.10 A |
| Rated current at 60°C according to IEC 60947                                              | 94.10 A  |
| Rated current 65°C according to IEC 60947                                                 | 91.10 A  |
| Rated current 70°C according to IEC 60947                                                 | 87.90 A  |

##### Architecture

|                           |                |
|---------------------------|----------------|
| Number of poles           | 4              |
| Control/operation element | Toggle         |
| Device construction type  | Fixed built-in |

##### Tripping

|                            |       |
|----------------------------|-------|
| Response time when opening | 10 ms |
|----------------------------|-------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Voltage

|                                                  |        |
|--------------------------------------------------|--------|
| Rated impulse withstand voltage U <sub>imp</sub> | 8000 V |
| Rated insulation voltage U <sub>i</sub>          | 690 V  |

##### Functions

|           |        |
|-----------|--------|
| Trip unit | TM F/F |
|-----------|--------|

##### Power

|                                       |      |
|---------------------------------------|------|
| Total power loss under I <sub>N</sub> | 39 W |
|---------------------------------------|------|

##### Endurance

|                                        |       |
|----------------------------------------|-------|
| Electric endurance in number of cycles | 10000 |
| Number of mechanical operations        | 20000 |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

##### Connection

|                                  |                        |
|----------------------------------|------------------------|
| Cross-section flexible conductor | 4 - 70 mm <sup>2</sup> |
| Cross-section rigid conductor    | 4 - 95 mm <sup>2</sup> |

##### Installation, mounting

|                               |       |
|-------------------------------|-------|
| Mounting-/Connection Position | Front |
|-------------------------------|-------|

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

---

**Settings**

|                                     |   |
|-------------------------------------|---|
| Thermal protection knob setting xIN | 1 |
|                                     | 1 |

---

**Dimensions**

|        |        |
|--------|--------|
| Height | 130 mm |
| Width  | 100 mm |
| Depth  | 68 mm  |

---

**Compatibility**

|                       |     |
|-----------------------|-----|
| Suitable for DIN Rail | Yes |
|-----------------------|-----|

---

**Main electrical attributes**

|                               |          |
|-------------------------------|----------|
| Magnetic protection trip time | 0 - 0 ms |
|-------------------------------|----------|

---

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |