


# Product Datasheet

## ARF920D



ARF920D



RCBO with dangerous arc detection 20A B curve 6kA Type A 30mA

### Technical Features

#### Electric current

Rated current	20 A
Rated current -25°C	24.80 A
Rated current at -20°C	24.36 A
Rated current -15°C	23.92 A
Rated current -10°C	23.47 A
Rated current -5°C	23.04 A
Rated current at 0°C	22.60 A
Rated current 5°C	22.16 A
Rated current 10°C	21.73 A
Rated current 15°C	21.29 A
Rated current at 20°C	20.85 A
Rated current 25°C	20.41 A
Rated current 30°C	20 A
Rated current 35°C	19.53 A
Rated current at 40°C	19.10 A
Rated current at 45°C	18.66 A
Rated current at 50°C	18.20 A
Rated current 55°C	17.78 A
Rated current 60°C	17.34 A
Rated current 65°C	16.90 A
Rated current 70°C	16.46 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 61009-1	6 kA

#### Architecture

Curve	B
Type of pole	1P+N

#### Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

#### Installation, mounting

Nominal tightening torque down terminal	2 - 2 Nm
---	----------

#### Electric current

Breaking and opening capacity I <sub>dm</sub>	6 kA
Rated residual operating current I <sub>dn</sub>	30 mA

#### Voltage

Rated insulation voltage U <sub>i</sub>	500 V
---	-------

#### Safety

Residual current type	A
-----------------------	---

#### Voltage

Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

#### Power

Total power loss under I <sub>N</sub>	6.08 W
---------------------------------------	--------

#### Use conditions

Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C

#### Endurance

Number of mechanical operations	4000
Electric endurance in number of cycles	2000

# Product Datasheet

## ARF920D

---

### Installation, mounting

Nominal tightening torque	2.10 - 2.10 Nm
---------------------------	----------------

### Capacity

Number of modules	3
-------------------	---

### Installation, mounting

Type of bottom connection for modular devices	biconnect quickbusbar
Type of top connection for modular devices	quickconnect

### Dimensions

Height	83 mm
Width	53.20 mm
Depth	70 mm

### Frequency

Frequency	50 - 50 Hz
-----------	------------