



TXB322



### Binary input 2 fold + LED output 2 fold, flush mounted, KNX

#### Technical Features

##### Architecture

|            |     |
|------------|-----|
| Bus system | KNX |
|------------|-----|

##### Settings

|                              |             |
|------------------------------|-------------|
| Supported configuration mode | ETS<br>easy |
|------------------------------|-------------|

##### Electric current

|                          |   |
|--------------------------|---|
| Number of entry circuits | 2 |
|--------------------------|---|

##### Equipment

|                                   |     |
|-----------------------------------|-----|
| External signal voltage necessary | Yes |
|-----------------------------------|-----|

##### Connectivity

|                           |    |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

##### Equipment

|                               |    |
|-------------------------------|----|
| Radio frequency bidirectional | No |
| With battery                  | No |
| With HVAC control             | No |

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Lighting

|                 |     |
|-----------------|-----|
| LED controlling | Yes |
|-----------------|-----|

##### Materials

|          |                |
|----------|----------------|
| Material | Polyamide (PA) |
| Colour   | Light grey     |
| RAL code | 7035           |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Use conditions

|                       |           |
|-----------------------|-----------|
| Operating temperature | 0 - 45 °C |
|-----------------------|-----------|

##### Voltage

|                            |                 |
|----------------------------|-----------------|
| Input voltage              | 5 - 5 V         |
| Operating voltage over bus | 21 - 32 V       |
| Type voltage supply        | DC              |
| System supply voltage      | 30 V DC Via bus |

##### Texts

|                    |                                            |
|--------------------|--------------------------------------------|
| Installation mode  | For flush-mounted and hollow wall mounting |
| Type of connection | With pre-assembled cable                   |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|