



MW310

MCB 3P 3kA C-10A 3M

Technical Features

Electric current

Rated current	10 A
---------------	------

Architecture

Type of pole	3P
Curve	C

Capacity

Number of modules	3
-------------------	---

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1	3 kA
--	------

Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

Voltage

Rated operational voltage U_e	230 - 400 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for massive conductors	1 - 35 mm ²

Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I^2t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

Power

Total power loss under I_N	5.80 W
------------------------------	--------

Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

Dimensions

Height	83 mm
Width	52.50 mm
Depth	70 mm

Sustainability	
RoHS conform	Yes