



FWB74N3

FWB encl.,univers,IP44,classII,240mod,interaxis 150mm,1100x1050x161mm

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Electric current**

Rated current 125 A

**Equipment**

Number of rails 22

Number of rows 22

Number of section in width 4

Has neutral terminal block No

**Capacity**

Number of modules 240

**Functions**

With conduit inlets Yes

**Dimensions**

Height 1100 mm

Width 1050 mm

Depth 165 mm

**Cover, door**

Number of cabinet doors 2

Number of locks 1

**Dimensions**

Number of width units 48

**Cover, door**

Type of handle Hinged pattern handle

Door/cover is transparent No

**Connectivity**

Mounting type Surface mounting

**Materials**

Material Steel

RAL code 9010

Colour Pure white

**Equipment**

Has earthing terminal block No

Has mounting plate No

**Safety**

Protection class Isolation class II

Ingress Protection (IP) class IP44

Locking type Bar lock

**Sustainability**

RoHS conform Yes