



MU463A

MCB 4P 6kA C-63A 4M

Technical Features

Electric current

Rated current	63 A
Rated current -15°C	76.20 A
Rated current -10°C	74.90 A
Rated current -5°C	73.50 A
Rated current at 0°C	72.10 A
Rated current 5°C	70.70 A
Rated current 10°C	69.20 A
Rated current 15°C	67.70 A
Rated current at 20°C	66.20 A
Rated current 25°C	64.60 A
Rated current 30°C	63 A
Rated current 35°C	61.40 A
Rated current at 40°C	59.70 A
Rated current at 45°C	57.90 A
Rated current at 50°C	56.10 A
Rated current 55°C	54.30 A
Rated current 60°C	52.40 A
Rated current 65°C	50.70 A
Rated current 70°C	48.90 A

Architecture

Type of pole	4P
Curve	C

Capacity

Number of modules	4
-------------------	---

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	6 kA
---	------

Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

Voltage

Rated operational voltage U _e	230 - 400 V
Type voltage supply	AC
Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for massive conductors	1 - 35 mm ²
Cross-section flexible conductor	1 - 25 mm ²
Cross-section rigid conductor	1 - 35 mm ²

Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
--	---

Air humidity protection	For all climates
-------------------------	------------------

Operating temperature	-25 - 70 °C
-----------------------	-------------

Power

Total power loss under IN	24.63 W
---------------------------	---------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Top connection alignment for modular devices	Aligned terminal
--	------------------

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	83 mm
--------	-------

Width	70 mm
-------	-------

Depth	70 mm
-------	-------

Sustainability

RoHS conform	Yes
--------------	-----
