



286110

Universal Rotary Dimmer with Soft Lock

Technical Features

Voltage

| | |
|-------------------|-------------|
| Operating voltage | 230 - 230 V |
|-------------------|-------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Materials

| | |
|----------|------------------|
| Material | Metal Plastic |
|----------|------------------|

Dimensions

| | |
|---------------|-------|
| Diameter axis | 4 mm |
| Height | 71 mm |
| Width | 71 mm |
| Depth | 50 mm |

Architecture

| | |
|---------------------------|------------------------|
| Control/operation element | Push & rotative switch |
|---------------------------|------------------------|

Texts

| | |
|----------------------|---|
| Dimming principle | Phase cut-on or cut-off according to load type, self-learning |
| Fuse | Short-circuit and overload-proof (electronic fuse) |
| Voltage | Voltage test possible without dismantling |
| Installation mode | With spreader claws |
| Type of connection | With plug-in terminals |
| Extension unit input | With input for extension units insert for universal rotary dimmer |

Equipment

| | |
|------------------|-----|
| Substation input | Yes |
|------------------|-----|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |