




EW064_C

Industrial contactor 64A-AC3 / coil 220V 50-60Hz

Technical Features

Architecture

Type of pole	3P
--------------	----

Voltage

Rated operational voltage U _e	690 - 690 V
Command voltage AC	220 - 220 V
Command voltage DC	0 - 0 V
Rated operational voltage U _e AC for auxiliary contact	660 V
Rated insulation voltage U _i	1000 V

Electric current

Rated operational current I _e under 3P 220 - 230 V AC3 according to IEC 60947 - 4	65 A
Acceptable current rating AC3	64 A
Rated operational current I _e under 3P 380 - 400 V AC AC3 according to IEC 60947 - 4	64 A
Rated current I _e for auxiliary contact under 110 V AC AC15	6 A
Rated current I _e for auxiliary contact under 24 V AC AC15	6 A

Dimensions

Depth	108.70 mm
-------	-----------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Total power loss under I _N	6.80 W
Power dissipation per coil	6.80 W
Operating consumption	30 VA
Inrush power absorbed	280 VA
Rated operational power for 3P under 220 - 230 V AC AC3 according to IEC 60947 - 4	18.50 kW

Endurance

Number of mechanical operations	5000000
Electric endurance in number of cycles	500000

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Equipment

Number of auxiliary contacts as normally open contact	2
Number of auxiliary contacts as normally closed contact	2
Number of NO contacts	3
Number of NC contacts	0

Use conditions

Operating temperature	-20 - 55 °C
Storage/transport temperature	-40 - 80 °C

Connection

Cross-section of input and output with screws, for flexible conductors	10 - 35 mm ²
Cross-section of input and output with screws, for massive conductors	10 - 35 mm ²

Sustainability

Halogen free	Yes
RoHS conform	Yes