



HEW631LR

**Moulded Case Circuit Breaker h3+ P630 LSIG 4P4D N0-50-100% 630A 70kA FTC**

**Technical Features**

**Electric current**

Rated current	630 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 230 V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 415 V AC IEC 60947-2	70 kA
Breaking capacity on 1-pole for AC 230 V IEC 60947-2	10 kA
Breaking capacity on 1-pole for AC 400 V IEC 60947-2	10 kA

**Architecture**

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Left

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Electric current**

Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 690 V AC IEC 60947-2	12 kA
Rated service breaking capacity I <sub>cs</sub> under 220 V AC according to IEC 60947-2	100 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	100 kA
Rated service breaking capacity I <sub>cs</sub> under 240 V AC according to IEC 60947-2	100 kA
Rated service breaking capacity I <sub>cs</sub> under 380 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I <sub>cs</sub> under 415 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I <sub>cs</sub> under 690 V AC according to IEC 60947-2	12 kA
Rated current 10°C according to IEC 60947	630 A
Rated current 15°C according to IEC 60947	630 A
Rated current 20°C according to IEC 60947	630 A
Rated current 25°C according to IEC 60947	630 A
Rated current 30°C according to IEC 60947	630 A
Rated current at 35°C according to IEC 60947	630 A
Rated current at 40°C according to IEC 60947	630 A
Rated current 45°C according to IEC 60947	630 A
Rated current 50°C according to IEC 60947	630 A
Rated current 55°C according to IEC 60947	630 A
Rated current at 60°C according to IEC 60947	622 A
Rated current 70°C according to IEC 60947	510 A
Rated current 65°C according to IEC 60947	570 A

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Settings**

I <sub>r1</sub> current dial setting	250 A
	300 A
	350 A
	370 A
	400 A
	500 A
	600 A
	630 A
Adjustment range short-term delayed short-circuit release	375 - 6300 A

**Installation, mounting**

Nominal tightening torque	18 - 18 Nm
Mounting-/Connection Position	Front

<b>Voltage</b>	
Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 690 V
<b>Functions</b>	
Trip unit	LSIG
<b>Power</b>	
Total power loss under IN	119 W
Power loss per pole at In	39.6 W
<b>Equipment</b>	
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
<b>Safety</b>	
Ingress Protection (IP) class	IP4X
<b>Use conditions</b>	
Operating temperature	-25 - 70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
<b>Connection</b>	
Connector/plug type	Terminal
<b>Cable</b>	
Cable material	Copper Aluminium
<b>Dimensions</b>	
Height	260 mm
Depth	150 mm
<b>Controls and indicators</b>	
Motor drive integrated	No
<b>Compatibility</b>	
Suitable for DIN Rail	No
Compatible with RDC AOB	Yes
Suitable for distribution board	Yes
<b>Power supply</b>	
Position power supply	Bidirectional
<b>Electrical protection</b>	
Long-time overload protection (ltd): delay (tr)	0.5 s 1.5 s 2.5 s 5 s 7.5 s 9 s 10 s 12 s 14 s 16 s
Short-time protection (std): current (Isd)	1.5 2 3 4 5 6 7 8 10

---

**Electrical protection**

Short-time protection (std): delay (tsd)	50 ms 100 ms 200 ms 300 ms 400 ms
--	---

---

Instantaneous protection (li): dial setting coefficient	3 4 5 6 7 8 9 10 11
---	---

---

**Sustainability**

---

RoHS conform	Yes
--------------	-----