



EC370

**3Ph Kwhmeter via CT**

**Technical Features**

**Architecture**

Type of pole	3P+N
--------------	------

**Electric current**

Rated current	6000 A
---------------	--------

**Capacity**

Number of modules	4
-------------------	---

**Dimensions**

Height	90 mm
Width	72 mm

**Equipment**

Type of pulse generator	Electrical
-------------------------	------------

**Compatibility**

Suitable for	Purchase
--------------	----------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Measurement**

Measuring system	Measurement transformer
Type of measuring instrument	Electronic
Frequency measuring range	50 - 60 Hz

**Power supply**

Number of phases for power supply	4
-----------------------------------	---

**Functions**

Accuracy class	B
Tariff type	One-tariff

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-10 - 55 °C
Storage/transport temperature	-20 - 70 °C

**Power**

Power consumption VA	8.40 VA
Total power loss under IN	1.80 W

**Electric current**

Maximum measuring circuit current	6000 A
-----------------------------------	--------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes